



measuring microscope series 2008

The small instrument to fit in your briefcase

Order-no.	specifications	Price in €
	<p>all microscopes are focussed by the coaxial rotation of the barrel The ocular can be focused to the scale, which is not build into the ocular. The measuring scale is separately fitted above the cylinder in a receptacle. Since the scale can be rotated within the microscope, the whole instrument don't need to be turned.</p>	
PM-2008-25	Magnification: 25x Graduation:0,05 mm Field of view: 3,3 mm	150,00
PM-2008-50	Magnification: 50x Graduation:0,02 mm Field of view: 2 mm	160,00
PM-2008-75	Magnification: 75x Graduation:0,01 mm Field of view: 1,1 mm	170,00
PM-2008-100	Magnification: 100x Graduation:0,005 mm Field of view: 0,84 mm	200,00
PM-2008-LH 	Lighting for microscope 2008	25,00